

Garant
SNMG 190616, Grade: HB7120-1


Order data

Order number	251238 HB7120-1
GTIN	4045197928313
Item class	21G

Description

SNMG 190616 HB7120-1 Corner radius: 1.6 mm
 Grade: HB7120-1
 Chip breaker: VM
 Cutting depth a_p : 0.5 - 4 mm
 Feed f : 0.1 - 0.4 mm/rev.
 Cutting speed v_c main application: 80 - 260 m/min

Technical description

Cutting depth a_p	0.5 - 4 mm
Cutting conditions	continuous
Cutting speed v_c main application	80 - 260 m/min
Main application	M
Feed f	0.1 - 0.4 mm/rev.
Chip breaker	VM
Corner radius	1.6 mm

Grade	HB7120-1
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	SNMG 190616
Number of changes/inserts	8
Type of product	Indexable insert for turning