


HOLEX CleverDrill HSS jobber drill, uncoated, Ø DC h8: 3,8mm

Order data

Order number	113005 3,8
GTIN	4045197952073
Item class	12B

Description
Version:

Sturdy drills for all standard applications. Improved spot drilling behaviour due to cross-ground form. Standard core thickness and core taper. Profile ground. Surface: Bronze-coloured tempered helical flutes.

Recommendation:
Maximum drilling depth:

$$L_2 = L_c - 1.5 \times D_c.$$

Technical description

Feed f in steel < 750 N/mm ²	0.05 mm/rev.
Standard	DIN 1897
Tolerance nominal Ø	h8
Shank Ø D _s	3.8 mm
Overall length L	55 mm
recommended maximum drilling depth L ₂	16.3 mm
Number of cutting edges Z	2
Nominal Ø D _c	3.8 mm
Flute length L _c	22 mm
Point angle	130 degrees
Shank	Plain shank
Series	CleverDrill

Coating	uncoated
Tool material	HSS
Type	N
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
Alu plastics	suitable only under restricted conditions	80 m/min	N
Aluminium (short chipping)	suitable only under restricted conditions	63 m/min	N
Alu > 10% Si	suitable only under restricted conditions	50 m/min	N
Steel < 500 N/mm ²	suitable	35 m/min	P
Steel < 750 N/mm ²	suitable	32 m/min	P
Steel < 900 N/mm ²	suitable	25 m/min	P
Steel < 1100 N/mm ²	suitable only under restricted conditions	20 m/min	P
GG(G)	suitable only under restricted conditions	30 m/min	K
CuZn	suitable	40 m/min	N
Oil	suitable		
wet maximum	suitable		