

**Garant****SNMG 150608, Grade: HB7120-1**

## Order data

Order number	251230 HB7120-1
GTIN	4045197928153
Item class	21G

## Description

SNMG 150608 HB7120-1 Corner radius: 0.8 mm  
Grade: HB7120-1  
Chip breaker: VM  
Cutting depth  $a_p$ : 0.5 - 4 mm  
Feed  $f$ : 0.1 - 0.4 mm/rev.  
Cutting speed  $v_c$  main application: 80 - 260 m/min

## Technical description

Corner radius	0.8 mm
Main application	M
Cutting depth $a_p$	0.5 - 4 mm
Cutting speed $v_c$ main application	80 - 260 m/min
Feed $f$	0.1 - 0.4 mm/rev.
Cutting conditions	continuous
Grade	HB7120-1

Chip breaker	VM
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Tool material	Carbide
ISO code indexable insert	SNMG 150608
Number of changes/inserts	8
Type of product	Indexable insert for turning