



## Hi5 high feed rate indexable face mill, with bore, Ø D / number of teeth Z: 42/3\_ mm

### Order data

Order number	213110 42/3_
GTIN	4045197953940
Item class	210

### Description

#### Description:

Powerful and smooth-cutting high feed rate indexable face mill.  
Particularly smooth-running, due to unequal spacing of the teeth.  
Can also be used for semi-finishing.  
Cost-efficiency due to 5-edge inserts.

#### Note:

Use GARANT torque screwdriver TQ No. **211750 size 5.7** with bit No. **674252 size 20IP**.  
Spacing of the milling cutter's cutting edges: unequal spacing  
Through-coolant: true  
Tool exchange: PowerCard

### Technical description

Milling head suitable for insert shape	
Setting angle $\kappa$	degrees
Milling application	
Setting angle $\kappa$	degrees
Shank type	with bore
Through-coolant	yes
Setting angle $\kappa$	degrees
Machining strategy	
Tool exchange	PowerCard
Spacing of the cutters	unequal spacing

Norm

Type of product

\_\_\_\_\_

\_\_\_\_\_