

## Garant

### Solid carbide milling cutter with more chip separators TPC, TiAlN, Ø f8 DC: 16mm



#### Order data

Order number	203108 16
GTIN	4045197954190
Item class	11X

#### Description

##### Version:

High-performance milling cutter with **irregular cutter spacing** and **irregular helical pitch**. Optimised bending strength due to the use of ultra-fine grain substrates.

**Chip separator for controlled chip breaking.**

##### Note:

$h_{max}$ : The values stated in the table are maximum values.

$a_{e max} = 0.03 \times D$  for TPC machining.

Tolerance nominal Ø: f8

No. of teeth Z: 7

Helix angle: 40 °

Direction of infeed: horizontal and oblique

Shank: DIN 6535 HB to h6

Balance quality with shank: G 2.5 with HB

No. of teeth Z: 7

Flute length  $L_c$ : 80 mm

Overall length L: 136 mm

Shank Ø  $D_s$ : 16 mm

Corner chamfer width at 45°: 0.32 mm

Average chip thickness  $h_{max}$  for TPC milling in INOX < 900 N/mm<sup>2</sup>: 0.057 mm

#### Technical description

Cutting edge Ø $D_c$	16 mm
Flute length $L_c$	80 mm
Helix angle	40 °

Tolerance nominal $\varnothing$	f8
Shank $\varnothing D_s$	16 mm
Direction of infeed	horizontal and oblique
Balance quality with shank	G 2.5 with HB
Shank	DIN 6535 HB to h6
Average chip thickness $h_{max}$ for TPC milling in INOX < 900 N/mm <sup>2</sup>	0.057 mm
Corner chamfer width at 45°	0.32 mm
Overall length L	136 mm
No. of teeth Z	7
Corner chamfer angle	45 °
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	N
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width $a_e$ for milling operation	0.03×D
Through-coolant	no
Machining strategy	TPC
Colour ring	blue
Type of product	End / face mill

## User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	270 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	240 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	210 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	160 m/min	P

INOX < 900 N/mm <sup>2</sup>	suitable	200 m/min	M
INOX > 900 N/mm <sup>2</sup>	suitable	140 m/min	M
wet maximum	Suitable		
wet minimum	Suitable only under restricted conditions		
Air	suitable		