

HOLEX

Face mill arbor with cooling channel bore, HSK-A 100 A = 100, Spigot Ø d1: 22mm



Order data

Order number	306687 22
GTIN	4045197954343
Item class	32A

Description

Version:

- Clamping Ø 40 with 4 tapped holes for drive blocks to DIN 2079.
- With Balluff/RFID chip bore.
- Increased collar contact surface.
- HSK mating faces machined.

With cooling channel bores.

Application:

For clamping shell end mills and milling cutter heads.

Supplied with:

Lock screw.

Optional extras:

Coolant tube No. 309880, socket wrench for coolant tubes No. 309890, toggle spanner No. 309840.

Technical description

Milling mandrel length L ₄	19 mm
Suitable toggle spanner No. 309840	22
External Ø D	50 mm
Overhang dimension A	100 mm

Spare milling cutter lock screw No. 309860 / 309861	22
Clamping $\varnothing D_1$	22 mm
Adapter	HSK-A 100 A = 100
Arbor standard	ISO 12164-1
Arbor standard	DIN 69882-3
Arbor standard	DIN 69893
Shape	A
Cooling channel bore	not pluggable
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	$\leq 6 \mu\text{m}$
Machining strategy	HPC
Type of product	Milling head arbor