



## MaxX lifting magnet, maximum loading capacity (level): 1000kg



### Order data

Order number	382001 1000
GTIN	2050001944061
Item class	38D

### Description

#### Version:

Compact robust design with neodymium permanent magnets. Stray magnetic flux is prevented by the "neutral crown" principle, thus preventing undesirable attraction forces acting on adjacent loads. The base body is made from a single block without any weld seams, thus ensuring constant capability. The lever has a lock which prevents accidental release of the load. Certified break-away force.

#### Application:

Quick and easy handling and transport of flat and round materials with 3-fold safety.

### Technical description

maximum lifting capacity flat	1000 kg
maximum Ø round	450 mm
Dimension F	225 mm
minimum material wall thickness, flat	40 mm
Dimension E	88 mm
Dimension A	284 mm
Dimension C	133 mm

maximum lifting capacity round	400 kg
Weight	36 kg
minimum material wall thickness, round	25 mm
Dimension G	52 mm
maximum length flat	3000 mm
Dimension D	131 mm
Dimension B	342 mm
Type of product	Lifting magnet