



Permanent magnetic chuck, with parallel pole distribution, Chuck Ø: 350mm



Order data

| | |
|--------------|---------------|
| Order number | 380777 350 |
| GTIN | 2050001949264 |
| Item class | 33S |

Description

Version:

Powerful magnetic system with **neodymium** magnets and low magnetic field height.

Continuously adjustable magnetic force.

Application:

For grinding and turning.

For clamping small and thin to large workpieces.

Note:

The centre can be bored out to size "J".

Technical description

| | |
|---------------------|-----------|
| Height tolerance | 0 / -1 mm |
| Centring hole depth | 5 mm |
| Pitch circle Ø | 334 mm |
| Height | 62 mm |
| Thread Ø | 4×M8 |

| | |
|---|-------------------------|
| Centre Ø | 300 mm |
| Weight | 43 kg |
| Chuck Ø | 350 mm |
| possible to bore out to centre hole "J" | 25×20 mm |
| Nominal clamping force | 150 N/cm ² |
| Parallel pole distribution | 12+3 mm |
| Magnetic field height | 10 mm |
| Grinding allowance in pole area | 6 mm |
| Type of product | Magnetic clamping chuck |