

**Platform trolley, Type: 2501****Order data**

Order number	919800 2501
GTIN	4017976025018
Item class	96F

**Description****Version:**

Welded steel sections and tubes, platform made of chipboard with beech grain effect surface. 2 fixed wheels and 2 castors (with parking brake) and TPE tyres, hubs with grooved ball bearings.

**Standard:**

**EN 1757-3**

**Colour:**

Brilliant blue RAL 5007 **powder-coated**.

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

**Technical description**

Standard	EN 1757-3
Wheel Ø	200 mm
Width	1125 mm
Safe working load	600 kg
Material of wheel	TPE
Platform area width	1000 mm

Platform area height	270 mm
Height	990 mm
Number of castors with parking brake	2
Type	2501
Number of fixed wheels without parking brake	2
Weight	27 kg
Depth	609 mm
Platform area depth	600 mm
Type of product	Platform trolley