

Garant
Solid carbide milling cutter, AlCrN, Ø e8 DC: 11,7 mm

Order data

Order number	201307 11,7
GTIN	4045197930217
Item class	11X

Description
Version:

Dimensions similar to **DIN 6527**.

Improved coating for general-purpose applications in steel and cast iron.

Through-coolant: no

Tolerance nominal Ø: e8

No. of teeth Z: 2

Helix angle: 30 degrees

Direction of infeed: horizontal, oblique and vertical

Shank: DIN 6535 HE to h6

No. of teeth Z: 2

Flute length L_c : 26 mm

Overhang length L_1 incl. recess: 38 mm

Recess Ø D_1 : 11.5 mm

Overall length L: 83 mm

Shank Ø D_s : 12 mm

Technical description

Flute length L_c	26 mm
Feed f_z for side milling in steel < 750 N/mm ²	0.09 mm
Overhang length L_1 incl. recess	38 mm
No. of teeth Z	2
Shank form	HB
Corner chamfer width at 45°	0.1 mm

Recess $\varnothing D_1$	11.5 mm
Cutting edge $\varnothing D_c$	11.7 mm
Tolerance nominal \varnothing	e8
Overall length L	83 mm
Helix angle	30 degrees
Shank $\varnothing D_s$	12 mm
Shank	DIN 6535 HE to h6
Feed f_z for slot milling in steel < 750 N/mm ²	0.06 mm
Direction of infeed	horizontal, oblique and vertical
Corner chamfer angle	45 degrees
Coating	AlCrN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Cutting width a_e for milling operation	Full slot cutting depth 1xD
Cutting width a_e for milling operation	0.3xD for side milling
Through-coolant	no
Colour ring	without
Type of product	End mill