

Garant
Solid carbide milling cutter, AlCrN, Ø e8 DC: 20 mm

Order data

Order number	202268 20
GTIN	4045197930873
Item class	11X

Description
Version:

Dimensions similar to **DIN 6527**.

Improved coating for general-purpose applications in steel and cast iron.

Note:
Successor product to No. 202080.

Through-coolant: no

Tolerance nominal Ø: e8

No. of teeth Z: 3

Helix angle: 30 degrees

Direction of infeed: horizontal, oblique and vertical

Shank: DIN 6535 HB to h6

No. of teeth Z: 3

Flute length L_c : 38 mm

Overhang length L_1 incl. recess: 54 mm

Recess Ø D_1 : 19.7 mm

Overall length L: 104 mm

Shank Ø D_s : 20 mm

Technical description

Shank	DIN 6535 HB to h6
Shank Ø D_s	20 mm
Helix angle	30 degrees
Direction of infeed	horizontal, oblique and vertical
Overhang length L_1 incl. recess	54 mm

Tolerance nominal \varnothing	e8
Corner chamfer width at 45°	0.1 mm
Feed f_z for side milling in steel < 750 N/mm ²	0.15 mm
Flute length L_c	38 mm
Feed f_z for slot milling in steel < 750 N/mm ²	0.1 mm
No. of teeth Z	3
Cutting edge $\varnothing D_c$	20 mm
Overall length L	104 mm
Recess $\varnothing D_1$	19.7 mm
Corner chamfer angle	45 degrees
Coating	AlCrN
Tool material	Solid carbide
Standard	DIN 6527
Type	N
Cutting width a_e for milling operation	0.3×D for side milling
Cutting width a_e for milling operation	Full slot cutting depth 1×D
Through-coolant	no
Colour ring	without
Type of product	End mill