

**Sweeper, Manufacturer's designation: SW250****Order data**

Order number	078550 SW250
GTIN	5715492191987
Item class	07C

Description**Version:**

Manually-guided sweepers with tool-less adjustment of side brush and main brush for optimum cleaning even under varying floor conditions.

Manually operated, **large collection hopper** and fold-away handle.

Suitable for indoor and outdoor use.

Application:

For hard floors and also for carpeted floors. Ideal for sweeping up leaves, small quantities of dry dirt, crown caps, cigarettes etc.

Supplied with:

Manually-guided sweeper, main sweeper roller, side brush, integral filter. Main cylindrical sweeping brush and two side brushes.

Technical description

Theoretical area output	3680 m ² /h
Container volume	38 l
Length	1470 mm

Working width with side brushes	920 mm
Width	920 mm
Manufacturer's designation	SW250
Weight	20 kg
Height	1120 mm
Type of product	Sweeper