



Short drill chuck Form A, SK 50, Clamping range: 2,5-16mm



Order data

Order number	301575 2,5-16
GTIN	4045197931825
Item class	32K

Description

Version:

For clockwise and anticlockwise rotation.
Burnished. With Balluff/RFID chip bore.

Supplied with:

Torx® chuck key with T-handle **for high clamping force.**

Optional extras:

Pull studs (PS) No. 308600 – 308806. Pull stud wrenches No. 308820; 308835.

Technical description

Spare Torx® chuck key No. 625220	TX25
External Ø D	50 mm
Clamping range	2.5 - 16 mm
Overhang dimension A	80 mm
Adapter	SK 50
Arbor standard	ISO 7388-1
Shape	A
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	≤ 50 µm

maximum tightening torque $M_{d\max}$	≤ 14 Nm
Balluffchip bore	yes
Type of product	Short drill chuck