




## Solid carbide milling cutter, TiAlN, Ø DC: 10mm



### Order data

Order number	203618 10
GTIN	4045197958815
Item class	12X

### Description

#### Version:

For **finishing operations**. Special geometry for optimum chip evacuation. For **profile milling as a finishing operation**. Very sturdy version with strengthened core.

### Technical description

Tolerance nominal Ø	h10
Feed $f_z$ for side milling in steel < 900 N/mm <sup>2</sup>	0.072 mm
Direction of infeed	horizontal
Flute length $L_c$	22 mm
Overall length $L$	72 mm
Shank	DIN 6535 HA to h6
No. of teeth $Z$	6
Shank Ø $D_s$	10 mm
Helix angle	45 degrees
Cutting edge Ø $D_c$	10 mm
Corner chamfer angle	90 degrees
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard

Type	N
Cutting width $a_e$ for milling operation	0.1×D for side milling
Through-coolant	no
Colour ring	without
Type of product	End / face mill

### User data

	Suitability	$V_c$	ISO code
Steel < 500 N/mm <sup>2</sup>	suitable	160 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	140 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	120 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	110 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	100 m/min	P
Steel < 55 HRC	suitable	70 m/min	H
Steel < 60 HRC	suitable	60 m/min	H
wet maximum	suitable		
wet minimum	Suitable only under restricted conditions		
dry	Suitable		
Air	Suitable		

### Services

Shank grinding Type HB	129100 HB
------------------------	-----------