

Garant

GARANT Diabolo solid carbide torus cutter R1 0.1, TiAlN, Ø DC × L1: 0,8X10mm



Order data

Order number	206156 0,8X10
GTIN	4045197934000
Item class	11X

Description

Version:

GARANT Diabolo:

Special geometry, coating and carbide **for hard machining in the high-performance field.**
Suitable even for machining **electrolytic copper.**

Double-relief ground with 2 chamfers hollow ground for high-precision hard machining.

Recess angle $\alpha = 16^\circ$.

Tolerances:

- **Corner radius: $R_1 = \pm 0.0025$ mm.**
- **Neck \varnothing : $D_1 = 0 / -0.01$ mm.**

Note:

At greater tool overhang lengths, use a reduced value for a_p !

Values for:

side milling: $a_p = 0.1 \times D \times a_{p,corr}$

copying: $a_p = 0.05 \times D \times a_{p,corr}$

To calculate the feed rate vf please use the actual speed of the machine (the maximum possible speed)! e.g: $vf = 18000$ [rpm] × fz [mm/Z] × z

Technical description

Shank	DIN 6535 HA to h5
Corner radius R_1	0.1 mm
Correction factor $a_{p,corr}$	0.35
No. of teeth Z	2
Helix angle	25 degrees

Recess $\varnothing D_1$	0.78 mm
Feed f_z for side milling in steel < 65 HRC	0.012 mm
Overhang length L_1 incl. recess	10 mm
Overall length L	50 mm
Flute length L_c	0.8 mm
Shank $\varnothing D_s$	4 mm
Feed f_z for copy milling in steel < 65 HRC	0.012 mm
Cutting edge $\varnothing D_c$	0.8 mm
Series	Diabolo
Coating	TiAlN
Tool material	Solid carbide
Standard	Manufacturer's standard
Type	H
Tolerance nominal \varnothing	0 / -0.005
Direction of infeed	horizontal, oblique and vertical
Cutting width a_e for milling operation	0.05×D for copy milling
Cutting width a_e for milling operation	0.05×D for copy milling
Through-coolant	no
Colour ring	red
Type of product	Torus cutter

User data

	Suitability	V_c	ISO code
Steel < 750 N/mm ²	suitable only under restricted conditions	200 m/min	P
Steel < 900 N/mm ²	suitable only under restricted conditions	200 m/min	P
Steel < 1100 N/mm ²	suitable	190 m/min	P
Steel < 1400 N/mm ²	suitable	170 m/min	P

Steel < 50 HRC	suitable	120 m/min	H
Steel < 55 HRC	suitable	100 m/min	H
Steel < 60 HRC	suitable	72 m/min	H
Steel < 65 HRC	suitable	55 m/min	H
Steel < 67 HRC	suitable	50 m/min	H
Steel < 70 HRC	suitable	45 m/min	H
INOX < 900 N/mm ²	suitable	90 m/min	M
INOX > 900 N/mm ²	suitable	80 m/min	M
CuZn	suitable	140 m/min	N
wet maximum	suitable only under restricted conditions		
wet minimum	suitable only under restricted conditions		
dry	suitable		
Air	suitable		