



Table trolley with 2 platforms, Type: 4840



Order data

Order number	919870 4840
GTIN	4017976348407
Item class	96F

Description

Version:

Welded steel construction, **oil-tight trays**.

2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings.

Upper **oil-tight tray** with **150 mm** high edge.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Type	4840
Material of wheel	TPE
Number of castors with parking brake	2
Number of fixed wheels without parking brake	2
Width	1021 mm

Height of bottom shelf	207 mm
Height of top shelf	829 mm
Platform area width	850 mm
maximum load capacity	400 kg
Weight	42 kg
Wheel Ø	160 mm
Height	880 mm
Load capacity of top shelf	200 kg
Standard	EN 1757-3
Platform area depth	500 mm
Depth	500 mm
Type of product	Table trolleys