



Folding trolley, Type: KW11



Order data

Order number	919810 KW11
GTIN	4017976011547
Item class	96F

Description

Version:

Welded steel frame with folding handle, 2 fixed wheels and 2 castors (with parking brake). Chipboard platform. TPE tyres, hubs with grooved ball bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Weight	24 kg
Height folded up	315 mm
Number of castors with parking brake	2
Number of fixed wheels without parking brake	2
Width folded up	995 mm

Platform area height	230 mm
Wheel Ø	160 mm
maximum load capacity	250 kg
Depth folded up	620 mm
Type	KW11
Platform area width	900 mm
Material of wheel	TPE
Standard	EN 1757-3
Platform area depth	600 mm
Type of product	Folding trolley