



HOLEX Pro Steel solid carbide drill, plain shank DIN 6535 HA, TiAlN, Ø DC h7: 6,3mm



Order data

| | |
|--------------|---------------|
| Order number | 123103 6,3 |
| GTIN | 4045197960337 |
| Item class | 12F |

Description

Version:

Straight major cutting edges and a **special flute profile** ensure good chip evacuation. The robust cutter geometry ensures high-performance drilling with good process reliability. A wide range of applications in steel materials thanks to a combination of tough ultra-fine grain carbide and extremely wear-resistant coating.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Versions with HB and HE shank available at the same price as HA.

For **HB shanks**: use order **No. 123104**.

For **HE shanks**: use order **no. 123109**.

Technical description

| | |
|--|-------------------------|
| recommended maximum drilling depth L_2 | 66.6 mm |
| Flute length L_c | 76 mm |
| Standard | Manufacturer's standard |
| Tolerance nominal \varnothing | h7 |
| Number of cutting edges Z | 2 |
| Overall length L | 114 mm |
| Feed f in steel < 900 N/mm ² | 0.16 mm/rev. |
| Nominal $\varnothing D_c$ | 6.3 mm |
| Shank $\varnothing D_s$ | 8 mm |

| | |
|--------------------|-------------------|
| Series | Pro Steel |
| Coating | TiAlN |
| Tool material | Solid carbide |
| Version | 8×D |
| Point angle | 135 degrees |
| Shank | DIN 6535 HA to h6 |
| Through-coolant | yes, with 25 bar |
| Machining strategy | HPC |
| Semi-Standard | yes |
| Colour ring | green |
| Type of product | Jobber drill |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu plastics | suitable only under restricted conditions | 250 m/min | N |
| Aluminium (short chipping) | suitable only under restricted conditions | 200 m/min | N |
| Alu > 10% Si | suitable only under restricted conditions | 160 m/min | N |
| Steel < 500 N/mm ² | suitable | 125 m/min | P |
| Steel < 750 N/mm ² | suitable | 115 m/min | P |
| Steel < 900 N/mm ² | suitable | 95 m/min | P |
| Steel < 1100 N/mm ² | suitable | 90 m/min | P |
| Steel < 1400 N/mm ² | suitable | 65 m/min | P |
| INOX < 900 N/mm ² | suitable | 35 m/min | M |
| INOX > 900 N/mm ² | suitable only under restricted conditions | 30 m/min | M |
| GG | suitable | 100 m/min | K |
| GGG | suitable | 65 m/min | K |

| | |
|-------------|----------|
| Uni | suitable |
| wet maximum | suitable |
| wet minimum | suitable |