

HOLEX**Gap sheet metal punch with ball thrust bearing, Punch Ø (hole Ø): 37mm****Order data**

Order number	834160 37
GTIN	2050000995637
Item class	86C

Description**Version:**

Consisting of matrix, punch, and draw bolt.

With ball thrust bearing and **split punch**, which cuts the waste material into 3 pieces. The cut pieces easily fall out of the matrix.

Application:

For punching holes into diverse materials such as sheet steel, sheet stainless steel, sheet aluminium, sheet copper etc. Particularly useful where access is difficult (e.g. large sheet metal plates, control cabinets, fuse boxes, junction boxes, dashboards, sink basins, bodywork etc.). Not suitable for pipework. It is imperative to grease the pressure screw and matrix before use.

Operation:

- using a **wrench**
- using **manual hydraulics** No. 834655 size 1.
- using a **manual hydraulic drive** No. 834700. **From 50 mm Ø upwards the use of the manual hydraulic drive is recommended.**

Material:

Special tool steel, burnished.

Note:

- When using hydraulic tools, use draw bolt No. 834070 (optional accessory) instead of the pressure screw.**
- Size 32 and 35 for holes in stainless steel sinks, to attach 1/2 inch sink fitments.**

Technical description

hole Ø to be pre-drilled	17 mm
for stainless sheet steel depending on tensile strength up to	1.75 mm
Punch Ø (hole Ø)	37 mm
for conduit threads to DIN 40430	PG29
Draw screw size	24 mm
Draw screw	M16×1.5×55
for material thickness (sheet metal St 37)	2.5 mm
Type of product	Punching tool

Accessories

Spare draw bolt for round sheet metal punches Thread Ø / Length 16/55 mm	834040 16/55
Spare ball bearing draw bolt for round sheet metal punches Thread Ø / Length 16/55 mm	834060 16/55