



Trolley with handle, Type: KF2



Order data

Order number	919805 KF2
GTIN	4017976011615
Item class	96F

Description

Version:

Welded steel tubes, platform made of chipboard.

2 fixed wheels and 2 castors (with parking brake) and TPE tyres, hubs with grooved ball bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Wheel Ø	125 mm
Height	860 mm
Number of fixed wheels without parking brake	2
Material of wheel	TPE
Platform area width	600 mm

Weight	11 kg
Width	890 mm
Safe working load	250 kg
Number of castors with parking brake	2
Standard	EN 1757-3
Height of bottom shelf	195 mm
Type	KF2
Platform area depth	500 mm
Depth	500 mm
Type of product	Trolley with handle