



## Enclosed trolley with 5 platforms, Type: 5392



### Order data

|              |               |
|--------------|---------------|
| Order number | 919882 5392   |
| GTIN         | 4017976013176 |
| Item class   | 96F           |

### Description

#### Version:

Steel angle section construction with tubular pushing handle. End walls, 1 side wall and roof clad with 40×40×4 mm wire mesh, fully welded. Positive bar locking with pivoting handle and padlock. 1 fixed platform and 4 loose shelves of chipboard with beech grain surface. Intermediate shelves adjustable at 100 mm intervals. The bottom shelf is not adjustable. 2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings. TOTALSTOP central braking system on the castors.

#### Standard:

**EN 1757-3**

#### Colour:

Brilliant blue RAL 5007 **powder-coated**.

### Technical description

|                   |           |
|-------------------|-----------|
| Standard          | EN 1757-3 |
| Height of shelf 5 | 1482 mm   |
| Push handle       | yes       |

|  |  |
|--|--|
| Height                                       | 1792 mm                                    |
| Number of fixed wheels without parking brake | 2  |
| Weight                                       | 144 kg                                     |
| Load capacity of each loose shelf            | 90 kg                                      |
| Width  | 1170 mm                                    |
| Type   | 5392                                       |
| Platform area width                          | 1000 mm                                    |
| Height of shelf 1                            | 292 mm                                     |
| Number of castors with parking brake         | 2  |
| Material of wheel                            | TPE  |
| Material of loose shelf                      | Sandwich boards with beech-effect surface. |
| Wheel Ø                                      | 200 mm                                     |
| Height of shelf 4                            | 1182 mm                                    |
| Total load capacity                          | 750 kg                                     |
| Height of shelf 2                            | 582 mm                                     |
| Height of shelf 3                            | 882 mm                                     |
| Depth  | 745 mm                                     |
| Platform area depth                          | 680 mm                                     |
| Height adjustment interval                   | 100  |
| Type of product                              | Enclosed trolley                           |