



## Table trolley with 2 platforms up to 1200 kg, Type: 12406



### Order data

Order number	919865 12406
GTIN	4017976124063
Item class	96F

### Description

**Version:**

Welded steel and sections and tubes, platforms made of non-slip platform of marine plywood. 2 fixed wheels and 2 castors (with parking brake), high-grade resilient solid blue-grey rubber treadless tyres (200x50 mm), and hubs with roller bearings.

**Standard:**

**EN 1757-3**

**Colour:**

Brilliant blue RAL 5007 **powder-coated**.

**Note:**

Supplied for self-assembly, saving freight costs. Delivered unassembled.

### Technical description

Height of top shelf	925 mm
Width	2210 mm
Depth	800 mm
Wheel Ø	200 mm
Standard	EN 1757-3
Load capacity of top shelf	500 kg

Type	12406
Number of castors with parking brake	2
Number of fixed wheels without parking brake	2
Platform area width	2000 mm
Material of wheel	Resilient solid rubber
Height	925 mm
Platform area depth	800 mm
maximum load capacity	1200 kg
Height of bottom shelf	283 mm
Weight	156 kg
Type of product	Table trolleys