

**Enclosed trolley, Type: 1552****Order data**

Order number	919877 1552
GTIN	4017976015521
Item class	96F

Description**Version:**

Enclosed trolley with one **removable** longitudinal side. Platform made of chipboard with beech grain surface finish, welded steel construction, 2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Wheel Ø	200 mm
Number of castors with parking brake	2
Number of fixed wheels without parking brake	2
Type	1552
Width	1180 mm

Material of wheel	TPE
Platform area height	270 mm
Platform area width	1000 mm
Height	990 mm
maximum load capacity	600 kg
Weight	45 kg
Platform area depth	700 mm
Depth	709 mm
Type of product	Enclosed trolley