

**Enclosed trolley, Type: 1553****Order data**

Order number	919877 1553
GTIN	4017976015538
Item class	96F

Description**Version:**

Enclosed trolley with one **removable** longitudinal side. Platform made of chipboard with beech grain surface finish, welded steel construction, 2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Height	990 mm
maximum load capacity	600 kg
Type	1553
Wheel Ø	200 mm
Number of castors with parking brake	2

Material of wheel	TPE
Weight	53 kg
Platform area width	1200 mm
Platform area height	270 mm
Width	1380 mm
Number of fixed wheels without parking brake	2
Platform area depth	800 mm
Depth	809 mm
Type of product	Enclosed trolley