



Table trolley with 2 platforms, Type: 4822



Order data

Order number	919870 4822
GTIN	4017976048222
Item class	96F

Description

Version:

Welded steel construction, **oil-tight trays**.

2 fixed wheels and 2 castors (with parking brake), TPE tyres, hubs with grooved ball bearings. **Oil-tight trays** with **40 mm** high edge.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Note:

Supplied for self-assembly, saving freight costs. Delivered unassembled.

Technical description

Material of wheel	TPE
Number of fixed wheels without parking brake	2
Number of castors with parking brake	2
Type	4822
Wheel Ø	200 mm

Load capacity of top shelf	200 kg
Height of bottom shelf	248 mm
Weight	47 kg
Platform area width	1000 mm
Width	1171 mm
Height of top shelf	870 mm
maximum load capacity	400 kg
Height	910 mm
Standard	EN 1757-3
Platform area depth	700 mm
Depth	700 mm
Type of product	Table trolleys