



Power Q high feed rate indexable milling cutter, with thread, Ø D / number of effective cutting edges Z: 40/3_ mm

Order data

Order number	212816 40/3_
GTIN	4045197938695
Item class	210

Description

Spare part:

Pack of insert screws No. 219812 (15IP; 5.0Nm).

Note:

When working with extensions, always use internal cooling.

Use GARANT torque screwdriver TQ No. **211750 size 5.0** with bit No. **674252 size 15IP**.

Milling application: Plunging

Milling application: Ramping

Milling application: Circular milling

Machining strategy: HPC

Tool exchange: PowerCard

Technical description

Setting angle κ	
Machining strategy	HPC
Tool exchange	PowerCard
Spacing of the cutters	
Shank type	with thread
Direction of infeed	
Milling application	Plunging
Milling application	Ramping
Milling application	Circular milling
Milling head suitable for insert shape	

Type of product
