

Garant

GARANT Power Q high feed rate indexable milling cutter, with threaded shank, $\varnothing D$ / number of effective cutting edges Z: 30/2mm


Order data

Order number	212816 30/2
GTIN	4045197939302
Item class	210

Description
Spare part:

Pack of insert screws No. 219812 (15IP; 5.0Nm).

Note:

Use GARANT torque screwdriver TQ No. **211750 size 5.0** with bit No. **674252 size 15IP**.
When working with extensions, always use internal cooling.

Technical description

$\varnothing D_3$	14 mm
Circular interpolation milling a_p	1.5 mm
Mounting thread M	M16
$\varnothing D_2$	29 mm
Number of cutting edges Z	2
Ramping length L for α_{max}	10.34 mm
Ramping angle α_{max}	4.42 degrees
Cutting edge $\varnothing D_c$	30 mm
suitable indexable insert	XDM.120516

Overall length L_{tot}	47 mm
Circular interpolation milling $\varnothing D_{min}$	44 mm
$\varnothing D_1$ h6	17 mm
Through-coolant	yes
Circular interpolation milling $\varnothing D_{max}$	58 mm
Series	Power Q
Shank type	with threaded shank
Milling application	Plunging
Milling application	Ramping
Milling application	Circular milling
Machining strategy	HPC
Tool exchange	PowerCard
Type of product	Copy mill

Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 15IP	674252 15IP
Torque screwdriver, fixed setting set torque 5,0 N·m	211750 5,0