

## Garant

**GARANT Power Tang 90° tangential high-performance shoulder mill wide pitch, with bore,  $\varnothing$  D / number of effective cutting edges Z: 40/4mm**



### Order data

Order number	215966 40/4
GTIN	4045197940018
Item class	210

### Description

#### Version:

Maximum stability due to tangentially arranged inserts.

High feed rate values for maximum metal removal rate due to optimum indexable insert with stability in the direction of the cutting force.

#### Note:

Use GARANT torque screwdriver TQ No. **211750 size 1.2** with bit No. **674252 size 8IP**.

### Technical description

Overall length $L_{tot}$	40 mm
maximum cutting depth $a_{p\ max}$	8 mm
Mounting bore $\varnothing$	16 mm
Cutting edge $\varnothing D_c$	40 mm
Pack of insert screws	219868 2 (8IP; 1.2 Nm)
suitable indexable insert	LO.U0904..
Number of cutting edges Z	4

Series	Power Tang
Shank type	with bore
Setting angle $\kappa$	90 degrees
Milling application	Corner milling
Spacing of the cutters	unequal spacing
Through-coolant	yes
Tool exchange	PowerCard
Type of product	End / face mill

---

## Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP
Torque screwdriver, fixed setting set torque 1,2 N·m	211750 1,2