

Garant

GARANT Power Tang 90° tangential high-performance shoulder mill close pitch, Plain shank, $\varnothing D$ / number of effective cutting edges Z: 25/4mm



Order data

Order number	215956 25/4
GTIN	4045197939920
Item class	210

Description

Version:

Maximum stability due to tangentially arranged inserts.

High feed rate values for maximum metal removal rate due to optimum indexable insert with stability in the direction of the cutting force.

Note:

Use GARANT torque screwdriver TQ No. **211750 size 1.2** with bit No. **674252 size 8IP**.

Technical description

Overhang L_1	30 mm
Cutting edge $\varnothing D_c$	25 mm
Number of cutting edges Z	4
suitable indexable insert	LO.U0904..
Shank $\varnothing D_s$ h6	25 mm
Pack of insert screws	219868 2 (8IP; 1.2 Nm)
maximum cutting depth $a_{p,max}$	8 mm
Overall length L_{tot}	120 mm
Series	Power Tang
Shank type	Plain shank
Setting angle κ	90 degrees

Milling application	Corner milling
Spacing of the cutters	unequal spacing
Through-coolant	yes
Tool exchange	PowerCard
Type of product	End / face mill

Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP
Torque screwdriver, fixed setting set torque 1,2 N·m	211750 1,2