

**Garant**
**GARANT Power Tang 90° tangential high-performance shoulder mill, with thread, Ø D / Zeff: 32/3mm**

**Order data**

Order number	215974 32/3
GTIN	4045197940117
Item class	210

**Technical description**

Pack of insert screws	219868 2 (8IP; 1.2 Nm)
maximum cutting depth $a_{p\ max}$	39 mm
Overall length $L_{tot}$	50 mm
Cutting edge $\varnothing D_c$	32 mm
Number of effective inserts $Z_{eff}$	3
$\varnothing D_2$	30 mm
$\varnothing D_1\ h6$	17 mm
Mounting thread M	M16
Series	Power Tang
suitable indexable insert	LO.U0904..
Number of indexable inserts	15
Shank type	with thread
Setting angle $\kappa$	90
Milling application	Corner milling

Spacing of the cutters	unequal spacing
Through-coolant	yes
Tool exchange	PowerCard
Type of product	End / face mill

---

## Accessories

PrecisionBit for Torx Plus®, 1/4 inch E 6.3 Torx Plus® profile 8IP	674252 8IP
Torque screwdriver, fixed setting set torque 1,2 N·m	211750 1,2