

## Tilting container with low overall height, painted, Skip volume: 500l



### Order data

Order number	919955 500
GTIN	2050001937445
Item class	94B

### Description

#### Version:

Tilting container **for solid materials** with **low overall height** and well-balanced centre of gravity. A pull cable allows the container to be tipped at any height.

The sheet steel body of the container has a strengthening profile around the edge and a sturdy base frame with slots for fork-lift forks. A catch prevents accidental slipping off or tipping.

Fork-lift slots internal dimensions A×D = 200×60 mm.

#### Colour:

Optional **paint finishes** light blue RAL 5012, yellow orange RAL 2000, fire red RAL 3000, 1 reseda green RAL 601, mouse grey RAL 7005.

### Technical description

Safe working load	1000 kg
Height	680 mm
Length	1440 mm
Weight	111 kg
Fork-lift fork socket pitch B	150 mm

Width	780 mm
Application range	for solids
Skip volume	500 l
Filling edge height	495 mm
Colour selection	RAL 5012, 2000, 3000, 6011, 7005
Type of product	Tilting containers

---

## Accessories

Set of wheels for tilting containers and swarf containers, polyamide, 4 pieces Load capacity / wheel 450 kg	919970 450
---	------------