


**Solid carbide milling cutter, TiAlN, Ø h10 DC: 8mm**

**Order data**

Order number	203510 8
GTIN	4045197964175
Item class	12X

**Description**
**Version:**

**High stability** and **extremely smooth cutting action due to at least 6 teeth**. Eccentric relief ground. **For profile milling as a finishing operation.**

**Technical description**

Cutting edge Ø D <sub>c</sub>	8 mm
Overall length L	63 mm
Feed f <sub>z</sub> for side milling in steel < 900 N/mm <sup>2</sup>	0.063 mm
Shank Ø D <sub>s</sub>	8 mm
No. of teeth Z	6
Helix angle	45 degrees
Direction of infeed	horizontal
Corner chamfer width at 45°	0.1 mm
Shank	DIN 6535 HA to h6
Flute length L <sub>c</sub>	19 mm
Tolerance nominal Ø	h10
Corner chamfer angle	45 degrees
Coating	TiAlN
Tool material	Solid carbide

Standard	DIN 6527
Type	N
Cutting width $a_e$ for milling operation	0.1×D for side milling
Through-coolant	no
Colour ring	without
Type of product	End / face mill

### User data

	Suitability	$V_c$	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	600 m/min	N
Alu > 10% Si	suitable only under restricted conditions	400 m/min	N
Steel < 500 N/mm <sup>2</sup>	suitable	190 m/min	P
Steel < 750 N/mm <sup>2</sup>	suitable	170 m/min	P
Steel < 900 N/mm <sup>2</sup>	suitable	160 m/min	P
Steel < 1100 N/mm <sup>2</sup>	suitable	95 m/min	P
Steel < 1400 N/mm <sup>2</sup>	suitable	85 m/min	P
INOX < 900 N/mm <sup>2</sup>	suitable	90 m/min	M
GG(G)	suitable	120 m/min	K
Uni	suitable only under restricted conditions		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		
Air	Suitable only under restricted conditions		

### Services

Shank grinding Type HB

129100 HB