


Solid carbide milling cutter, TiAlN, Ø h10 DC: 16mm

Order data

Order number	203510 16
GTIN	4045197964205
Item class	12X

Description
Version:

High stability and **extremely smooth cutting action due to at least 6 teeth**. Eccentric relief ground. **For profile milling as a finishing operation.**

Technical description

Shank Ø D _s	16 mm
Direction of infeed	horizontal
Helix angle	45 degrees
Flute length L _c	32 mm
Corner chamfer width at 45°	0.1 mm
Shank	DIN 6535 HA to h6
Feed f _z for side milling in steel < 900 N/mm ²	0.089 mm
Tolerance nominal Ø	h10
No. of teeth Z	6
Cutting edge Ø D _c	16 mm
Overall length L	92 mm
Corner chamfer angle	45 degrees
Coating	TiAlN
Tool material	Solid carbide

Standard	DIN 6527
Type	N
Cutting width a_e for milling operation	$0.1 \times D$ for side milling
Through-coolant	no
Colour ring	without
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium (short chipping)	suitable only under restricted conditions	600 m/min	N
Alu > 10% Si	suitable only under restricted conditions	400 m/min	N
Steel < 500 N/mm ²	suitable	190 m/min	P
Steel < 750 N/mm ²	suitable	170 m/min	P
Steel < 900 N/mm ²	suitable	160 m/min	P
Steel < 1100 N/mm ²	suitable	95 m/min	P
Steel < 1400 N/mm ²	suitable	85 m/min	P
INOX < 900 N/mm ²	suitable	90 m/min	M
GG(G)	suitable	120 m/min	K
Uni	suitable only under restricted conditions		
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		
Air	Suitable only under restricted conditions		

Services

Shank grinding Type HB

129100 HB