

**Tipper truck RAL 5007 with discharge valve, Skip volume: 600l****Order data**

Order number	919920 600
GTIN	4017976147031
Item class	96D

Description**Version:**

Oil-tight welded skip, on bearings for tipping.

Skip edge folded over twice at the top.

Chassis with integral fork lift slots, standing area and tilt lock.

2 fixed wheels and 2 castors (with parking brake) with TPE tyres, hubs with grooved ball bearings.

TOTALSTOP - central braking system to EN 1757-3 fitted as standard to the castors.

Callout:

Discharge valve with sieve for separating liquids from solids.

Tipping action is operated manually.

For emptying using a forklift truck or when heavily loaded we recommend a self-tipper.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated.**

Technical description

Internal dimension at intake: width	194 mm
Width	855 mm

Bucket height	735 mm
Number of wheels	4
Material of wheel	TPE
Length	1458 mm
Internal dimension at intake: height	72 mm
Tipping mechanism	manual
Bucket length	1321 mm
Filling edge height with rollers	843 mm
Safe working load	750 kg
Height	1099 mm
Pull cord	no
Number of castors with parking brake	2
welded oil-tight	yes
Fork-lift fork socket pitch B	327 mm
Drain cock version	Delivery tap with sieve
Weight	95 kg
Bucket width	794 mm
Tipping prevention	yes
Wheel Ø	200 mm
Fork insertion slots dimension D	72 mm
Fork insertion slots dimension C	727 mm
Number of fixed wheels without parking brake	2
Fork insertion slots dimension A	194 mm
Skip volume	600 l
with fork insertion slots	yes
Colour	brilliant blue RAL 5007
Standard	EN 1757-3
Type of product	Tilting containers

