

Swarf-bucket truck with perforated plate insert, Skip volume: 250l



Order data

Order number	919935 250
GTIN	2050001936776
Item class	94B

Description

Version:

The **container is oil-tight and watertight**; it can be **discharged on level ground** and is fitted with a perforated plate insert and a drain valve.

The container has slots and catches to prevent accidental slipping and tipping. Supplied with 2 solid rubber wheels and 1 castor with a parking brake.

Colour:

Optional **paint finishes** light blue RAL 5012, yellow orange RAL 2000, fire red RAL 3000, reseda green RAL 6011, mouse grey RAL 7005.

Technical description

Number of castors with parking brake	1
Number of wheels	3
Fork insertion slots dimension D	55 mm
Safe working load	300 kg
welded oil-tight	yes
with fork insertion slots	yes
Perforated panel fittings	Perforated panel insert
Width	820 mm

Internal dimension at intake: height	55 mm
Skip volume	250 l
Internal dimension at intake: width	170 mm
Material of wheel	Solid rubber
Length	1115 mm
can be discharged on level ground	yes
Height	990 mm
Drain cock version	Delivery tap without sieve
Weight	77 kg
Fork-lift fork socket pitch B	465 mm
Fork insertion slots dimension A	170 mm
Filling edge height with rollers	680 mm
Number of fixed wheels without parking brake	2
Usable width	540 mm
Colour selection	RAL 5012, 2000, 3000, 6011, 7005
Type of product	Tilting containers