

Swarf-bucket truck with perforated plate insert, Skip volume: 400l



Order data

Order number	919935 400
GTIN	2050001936783
Item class	94B

Description

Version:

The **container is oil-tight and watertight**; it can be **discharged on level ground** and is fitted with a perforated plate insert and a drain valve.

The container has slots and catches to prevent accidental slipping and tipping. Supplied with 2 solid rubber wheels and 1 castor with a parking brake.

Colour:

Optional **paint finishes** light blue RAL 5012, yellow orange RAL 2000, fire red RAL 3000, reseda green RAL 6011, mouse grey RAL 7005.

Technical description

Fork-lift fork socket pitch B	465 mm
Number of fixed wheels without parking brake	2
welded oil-tight	yes
Perforated panel fittings	Perforated panel insert
Material of wheel	Solid rubber
Height	1090 mm
Weight	93 kg

Width	900 mm
Internal dimension at intake: height	55 mm
can be discharged on level ground	yes
Filling edge height with rollers	740 mm
Length	1320 mm
Safe working load	300 kg
Fork insertion slots dimension A	170 mm
Number of wheels	3
Number of castors with parking brake	1
Internal dimension at intake: width	170 mm
Drain cock version	Delivery tap without sieve
with fork insertion slots	yes
Skip volume	400 l
Fork insertion slots dimension D	55 mm
Usable width	620 mm
Colour selection	RAL 5012, 2000, 3000, 6011, 7005
Type of product	Tilting containers