



## Tipper truck RAL 7035 with discharge valve, Skip volume: 600l



### Order data

Order number	919922 600
GTIN	4017976847030
Item class	96D

### Description

#### Version:

Oil-tight welded skip, on bearings for tipping.

Skip edge folded over twice at the top.

Chassis with integral fork lift slots, standing area and protection against overturning.

2 fixed wheels and 2 castors (with parking brake) with TPE tyres, hubs with grooved ball bearings.

TOTALSTOP - central braking system to EN 1757-3 fitted as standard to the castors.

#### Callout:

Discharge valve

with sieve for separating liquids from solids.

Tipping action is operated manually.

For emptying using a forklift truck or when heavily loaded we recommend a self-tipper.

#### Standard:

**EN 1757-3**

#### Colour:

Light grey RAL 7035 **powder-coated.**

### Technical description

welded oil-tight	yes
------------------	-----

Safe working load	750 kg
Skip volume	600 l
Length	1458 mm
Internal dimension at intake: height	72 mm
Fork-lift fork socket pitch B	327 mm
Tipping prevention	yes
Number of fixed wheels without parking brake	2
Fork insertion slots dimension A	194 mm
Internal dimension at intake: width	194 mm
Number of castors with parking brake	2
Fork insertion slots dimension C	727 mm
Material of wheel	TPE
Number of wheels	4
Drain cock version	Delivery tap with sieve
Width	855 mm
Bucket height	735 mm
with fork insertion slots	yes
Height	1099 mm
Bucket length	1321 mm
Wheel Ø	200 mm
Bucket width	794 mm
Filling edge height with rollers	843 mm
Fork insertion slots dimension D	72 mm
Tipping mechanism	manual
Pull cord	no
Weight	95 kg
Colour	light grey RAL 7035
Standard	EN 1757-3
Type of product	Tilting containers

