

Tilting container with roller system, painted, Skip volume: 600l



Order data

Order number	919950 600
GTIN	2050001937407
Item class	94B

Description

Version:

Tilting container **for solid materials** with a well-balanced centre of gravity. A pull cable allows the container to be tipped at any height.

The sheet steel body of the container has a strengthening profile around the edge and a sturdy base frame with slots for fork-lift forks. A catch prevents accidental slipping off or tipping.

Fork-lift slots internal dimensions A×D = 200×80 mm.

Colour:

Optional **paint finishes** light blue RAL 5012, yellow orange RAL 2000, fire red RAL 3000, reseda green RAL 6011, mouse grey RAL 7005.

Technical description

Width	1070 mm
Weight	131 kg
Height	835 mm
Skip volume	600 l
Fork-lift fork socket pitch B	600 mm

with pull cord	yes
Safe working load	1000 kg
Application range	for solids
Tipping prevention	yes
Length	1260 mm
Filling edge height	740 mm
Colour selection	RAL 5012, 2000, 3000, 6011, 7005
Type of product	Tilting containers

Accessories

Set of wheels for tilting containers and swarf containers,
polyamide, 4 pieces Load capacity / wheel 450 kg

919970 450