

**Garant**
**Profile slotting toolholder for square cutting inserts  $\varnothing$  DS 20 mm, from square: 10mm**

**Order data**

Order number	290330 10
GTIN	4045197964397
Item class	29K

**Description**
**Note:**

- For machining centres, use the pull-up aid No. 290397 and a dial indicator to check the spindle orientation.
- For lathes without Y-axis, please use eccentric bush No. 290391 – 290393 for exact setting of the Y-coordinate.

**Technical description**

Screw	290399 1
Reach $L_1$	40 mm
Centre offset $L_3$	4.8 mm
Min. pre-drilling $-\varnothing D_{\min}$	9.1 mm
suitable for square drive	10 - 13 mm
Shank $\varnothing$	20 mm
Tool holder $\varnothing D_1$	10 mm
Through-coolant	yes
Shank length $L_s$	50 mm
Shank	Combination shank
Type of product	Keyway broaching and profile slotting tool

