

**Garant**
**Profile slotting toolholder for square cutting inserts  $\varnothing$  DS 32 mm, from square: 19mm**

**Order data**

Order number	290334 19
GTIN	4045197965455
Item class	29K

**Description**
**Note:**

- For machining centres, use the pull-up aid No. 290397 and a dial indicator to check the spindle orientation.
- For lathes without Y-axis, please use eccentric bush No. 290391 – 290393 for exact setting of the Y-coordinate.

**Technical description**

Reach $L_1$	89 mm
Centre offset $L_3$	10.25 mm
Min. pre-drilling $-\varnothing D_{\min}$	18.975 mm
Screw	290399 3
suitable for square drive	19 - 27 mm
Shank $\varnothing$	32 mm
Tool holder $\varnothing D_1$	18 mm
Through-coolant	yes
Shank length $L_s$	100 mm
Shank	Combination shank
Type of product	Keyway broaching and profile slotting tool

