

Garant
Profile slotting toolholder for hexagon cutting inserts \varnothing DS 32 mm, from hexagon: 37mm

Order data

Order number	290344 37
GTIN	4045197965691
Item class	29K

Description
Note:

- For machining centres, use the pull-up aid No. 290397 and a dial indicator to check the spindle orientation.
- For lathes without Y-axis, please use eccentric bush No. 290391 – 290393 for exact setting of the Y-coordinate.

Technical description

Reach L_1	126 mm
Screw	290399 3
Centre offset L_3	19.5 mm
Min. pre-drilling $-\varnothing D_{\min}$	37 mm
suitable for hexagon drive	37 - 45 mm
Shank \varnothing	32 mm
Tool holder $\varnothing D_1$	35 mm
Through-coolant	yes
Shank length L_s	100 mm
Shank	Combination shank
Type of product	Keyway broaching and profile slotting tool

