



Self-tipping truck with discharge valve, Skip volume: 600l



Order data

Order number	919925 600
GTIN	4017976160603
Item class	96D

Description

Version:

Sturdy welded construction of 3 mm sheet steel. Chassis with integral fork lift slots. 2 fixed wheels and 2 castors (with parking brake) with nylon tyres. Roll restraint and tip position locking, chain acts as protection against slipping off and tipping.

Callout:

Discharge valve with sieve for separating liquids from solids.

Tipping action is performed automatically when the interlock is released.

Pull cord to initiate tipping from the forklift seat position.

Standard:

EN 1757-3

Colour:

Brilliant blue RAL 5007 **powder-coated**.

Technical description

Fork insertion slots dimension D	90 mm
Tipping mechanism	Pull cord
Tipping prevention	yes
Drain cock version	Delivery tap with sieve

Safe working load	1500 kg
Fork-lift fork socket pitch B	582 mm
Filling edge height with rollers	981 mm
Width	1141 mm
Height	1070 mm
Internal dimension at intake: width	190 mm
Number of wheels	4
Length	1294 mm
Fork insertion slots dimension A	190 mm
Number of fixed wheels without parking brake	2
with fork insertion slots	yes
Fork insertion slots dimension C	982 mm
Skip volume	600 l
Internal dimension at intake: height	90 mm
Pull cord	yes
Wheel Ø	200 mm
Material of wheel	Polyamide
Weight	155 kg
Number of castors with parking brake	2
Colour	brilliant blue RAL 5007
Standard	EN 1757-3
Height without rollers	837 mm
Type of product	Tilting containers