

**Lifting table cart, Load capacity: 250kg****Order data**

Order number	919917 250
GTIN	4017976068329
Item class	96D

Description**Version:**

Profile steel / sheet steel construction with sturdy tubular steel pushing handle.

Hydraulic pump with chrome-plated piston. Operated by foot pedal. Lowering valve with precise control by hand lever.

2 fixed wheels and 2 castors (with parking brake) with polyurethane tyres.

Colour:

Anthracite grey RAL 7016 **powder-coated**.

Technical description

Wheel Ø	125 mm
Length	1020 mm
Load capacity	250 kg
Lift range	330 - 910 mm
Platform area length	830 mm
Width	500 mm

Weight	78 kg
Platform area width	500 mm
Type of product	Lifting table cart