



NC8 NC high pressure vice, Type: 90



Order data

Order number	360405 90
GTIN	4250364403252
Item class	34A

Description

Version:

Compact size: Optimum ratio between clamping range and overall length. The clamping force can be pre-set **without using tools: in 11 steps:** Jaw width 90 mm, **in 4 steps:** Jaw width 125 / 160 / 200 mm. Particularly rigid base body of GJS-60, **top and bottom faces ground; pairing accuracy 0.02 mm.**

Feature:

Fully enclosed low-maintenance nitrided spindle!

- **Increased service reliability.**
- **Optimised swarf protection.**
- **Minimised cleaning requirement.**

With 25H6 M10 holes at 200 mm pitch for zero-point clamping system.

Application:

Can be used horizontally or laterally, **since the side faces are ground to an accuracy of -0.05 mm.**

Supplied with:

2 stepped jaws (= standard!), 1 crank handle, 4 table clamps.

Optional extras:

- **Clamping stud No. 360025 - 25 M10.**

Note:

- **Dimensions/jaws interface NC 8 identical to the Allmatic TC / LC.**
- **NC 8 (No. 360405) supersedes the products LC (No. 360500) and TC (No. 360400).**
- **Sizes 125 MX and 125 LX are supplied with jaws No. 361295 125 and No. 361296 125.**
- **No end face holes for extensions included!**

Technical description

Base body length a	283 mm
Version	Zero-point clamping system
Clamping force up to maximum	28 kN
Clamping range d	91 - 217 mm
Longitudinal slot l H7	20 mm
r ±0.015	73 mm
Weight	15 kg
Clamping range b	0 - 126 mm
Jaw height h	34 mm
t	97 mm
Overall length L	339 mm
Base body height c -0.02	80 mm
Cross-slot n H7	20 mm
m	112 mm
Colour code for suitable accessories	NC8
Type	90
Number of threads for workpiece back-stop	3
Tenon width B ₁ -0.05	90 mm
Series	NC8
Type of product	Machine vice