



NC8 NC high pressure vice, Type: H200



Order data

Order number	360405 H200
GTIN	4250364403429
Item class	34A

Description

Version:

Compact size: Optimum ratio between clamping range and overall length. The clamping force can be pre-set **without using tools: in 11 steps:** Jaw width 90 mm, **in 4 steps:** Jaw width 125 / 160 / 200 mm. Particularly rigid base body of GJS-60, **top and bottom faces ground; pairing accuracy 0.02 mm.**

Feature:

Fully enclosed low-maintenance nitrided spindle!

- **Increased service reliability.**
- **Optimised swarf protection.**
- **Minimised cleaning requirement.**

Heavy Duty for very heavy machining.

Application:

Can be used horizontally or laterally, **since the side faces are ground to an accuracy of -0.05 mm.**

Supplied with:

2 stepped jaws (= standard!), 1 crank handle, 4 table clamps.

Note:

- **Dimensions/jaws interface NC 8 identical to the Allmatic TC / LC.**
- **NC 8 (No. 360405) supersedes the products LC (No. 360500) and TC (No. 360400).**
- **Sizes 125 MX and 125 LX are supplied with jaws No. 361295 125 and No. 361296 125.**
- **No end face holes for extensions included!**

Technical description

Weight	85 kg
$r \pm 0.015$	164 mm
Type	200
Clamping range b	0 - 246 mm
Overall length L	615 mm
Cross-slot n H7	20 mm
t	164 mm
Clamping force up to maximum	80 kN
Colour code for suitable accessories	NC8
Base body height c -0.02	140 mm
Version	Zero-point clamping system
Base body length a	530 mm
Jaw height h	60 mm
m	234 mm
Clamping range d	189 - 435 mm
Longitudinal slot l H7	20 mm
Number of threads for workpiece back-stop	5
Tenon width $B_1 -0.05$	202 mm
Series	NC8
Type of product	Machine vice