



## NC8 NC high pressure vice, Type: 200



### Order data

|              |               |
|--------------|---------------|
| Order number | 360405 200    |
| GTIN         | 4250364403412 |
| Item class   | 34A           |

### Description

#### Version:

**Compact size:** Optimum ratio between clamping range and overall length. The clamping force can be pre-set **without using tools: in 11 steps:** Jaw width 90 mm, **in 4 steps:** Jaw width 125 / 160 / 200 mm. Particularly rigid base body of GJS-60, **top and bottom faces ground; pairing accuracy 0.02 mm.**

#### Feature:

**Fully enclosed low-maintenance nitrided spindle!**

- **Increased service reliability.**
- **Optimised swarf protection.**
- **Minimised cleaning requirement.**

Base body same as size 160.

#### Application:

Can be used horizontally or laterally, **since the side faces are ground to an accuracy of -0.05 mm.**

#### Supplied with:

2 stepped jaws (= standard!), 1 crank handle, 4 table clamps.

#### Note:

- **Dimensions/jaws interface NC 8 identical to the Allmatic TC / LC.**
- **NC 8 (No. 360405) supersedes the products LC (No. 360500) and TC (No. 360400).**
- **Sizes 125 MX and 125 LX are supplied with jaws No. 361295 125 and No. 361296 125.**

### Technical description

| Version                                   | Zero-point clamping system |
|---|----------------------------|
| Clamping range b                          | 0 - 246 mm                 |
| Base body length a                        | 530 mm                     |
| Weight                                    | 60 kg                      |
| Type                                      | 200                        |
| Base body height c -0.02                  | 115 mm                     |
| Colour code for suitable accessories      | NC8                        |
| Overall length L                          | 615 mm                     |
| Jaw height h                              | 60 mm                      |
| Clamping range d                          | 189 - 435 mm               |
| Clamping force up to maximum              | 60 kN                      |
| Longitudinal slot l H7                    | 20 mm                      |
| r ±0.015                                  | 164 mm                     |
| t   | 164 mm                     |
| m   | 234 mm                     |
| Cross-slot n H7                           | 20 mm                      |
| Tenon width B <sub>1</sub> -0.05          | 164 mm                     |
| Number of threads for workpiece back-stop | 5                          |
| Series                                    | NC8                        |
| Type of product                           | Machine vice               |