

## Garant

**Face mill arbor cylindrical, with cooling channel bore, SK 50 A = 200, Spigot Ø d1: 22mm**



### Order data

|              |               |
|--------------|---------------|
| Order number | 301151 22     |
| GTIN         | 4045197942272 |
| Item class   | 31A           |

### Description

#### Version:

- Taper shank, spigot, and all contact surfaces are ground at the collar.
- With RFID / Balluffchip bore.
- Larger collar contact face.

**Vibration damped version, arbor with vibration-damping core.**

#### Advantage:

Significantly lower tendency to vibrate. Considerable increase in feed rate.

#### Supplied with:

Cutter lock screw and drive dog.

#### Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835, Special toggle spanner No. 309840. Milling cutter lock screws No. 309860; 309861.

#### Note:

Further sizes on request.

### Technical description

|                                       |               |
|---------------------------------------|---------------|
| Overhang dimension A                  | 200 mm        |
| Spigot Ø d <sub>1</sub>               | 22 mm         |
| Ø D <sub>2</sub>                      | 48 mm         |
| Milling mandrel length L <sub>4</sub> | 19 mm         |
| Adapter                               | SK 50 A = 200 |
| Standard                              | DIN 6357      |

|                                       |                      |
|---------------------------------------|----------------------|
| Arbor standard                        | ISO 7388-1           |
| Shape                                 | AD                   |
| Balance quality G at rotational speed | G 6.3 at 8,000 rpm   |
| Concentricity                         | $\leq 6 \mu\text{m}$ |
| Machining strategy                    | HPC                  |
| Vibration                             | damped               |
| Type of product                       | Milling head arbor   |