



## FlyMarker® mini 65/30 needle marker Cordless, Battery capacity: 2X5,2A·h



### Order data

Order number	085757 2X5,2
GTIN	2050001945952
Item class	04F

### Description

#### Version:

For permanent identification, marking, lettering of batch and series production parts of different materials (steel, stainless steel, aluminium, copper, brass, plastics, tool steel, hardened steels up to 62 HRC, etc.).

- **Powerful electro-magnetic marking needle drive.**
- **Simple intuitive software with password protection.**
- **High-resolution colour display.**
- **Marking preview for reliable marking.**
- **Unbreakable housing.**
- **Interfaces: USB-A, USB-B and Ethernet.**
- **Font: Dot matrix in a 5×7 or 9×13 grid, font height 1.0 – 10.0 mm and larger.**
- **Fonts for character heights greater than 10.0 mm on request.**
- **High-quality double linear guides for precise marking results.**
- **Round parts can be marked radially and axially, and also in an arc of a circle.**
- **Supplied with an HPGL pack (for marking individual logos and inspection symbols, CE marks etc.)**
- **Supplied with a convenience pack (e.g. for shift identification, pre-positioning, multiple marking, etc.)**
- **Internal memory for several hundred marking files, fonts and logos.**
- **Available in 15 languages.**

Extremely handy, 100% mobile **cordless manual marking system** with integral keyboard and high-resolution LC colour display.

Marking field: 65 × 30 mm.

### Standard:

For permanent identification / marking / lettering of batch and series production parts of different materials (steel, stainless steel, aluminium, copper, brass, plastics, tool steel, hardened steels up to 62 HRC, etc.).

- **Powerful electro-magnetic marking needle drive.**
- **Simple intuitive software with password protection.**
- **High-resolution colour display.**
- **Marking preview for reliable marking.**

### Supplied with:

Tool kit, solid carbide marking needle 90° adjustment bracket with non-slip coating, setting gauge, and carrying case, **2×18 V Li-ion rechargeable batteries**, charger.

### Note:

Optionally available: Magnetic holder plate No. 085758 65/30, pillar support No. 085783 MINI.  
maximum marker field height: 30 mm

Interface: USB interface

Battery capacity: 5.2 A·h

Nominal voltage: 18 V

Weight including rechargeable battery: 2.7 kg

## Technical description

Interface	USB interface
Character height	10 mm
Manufacturer's designation	FlyMarker® mini 65/30
Battery capacity	5.2 A·h
Number of rechargeable batteries contained	2
Power supply	Rechargeable battery-powered
Type of rechargeable battery	Lithium-ion
Nominal voltage	18 V
Weight including rechargeable battery	2.7 kg
maximum marker field width	65 mm
maximum marker field height	30 mm
Type of product	Needle marker

## Accessories

Pillar support for stationary operation / use Type MINI	085783 MINI
Marking needle for FlyMarker® Angle of the marking needle tip 60 °	085790 60
Marking needle for FlyMarker® Angle of the marking needle tip 90 °	085790 90
Magnetic holder plate for FlyMarker® mini Type 65/30	085758 65/30
Logo loading from file Type LOGO	085785 LOGO
Marking needle for FlyMarker® Angle of the marking needle tip 110 °	085790 110