

Garant
Cutting disc, high-performance version THIN, Disc Ø: 125mm

Order data

Order number	563277 125
GTIN	4045197967497
Item class	51M

Description
Version:

Thin version for quick and cost-effective cutting, with a long service life.

Specification:

A46R-BF.

Technical description

Bore Ø	22.23 mm
Disc Ø	125 mm
Shape description	flat
Disc thickness	1.6 mm
Specification	A46R-BF
for material thicknesses	7.7 mm
Grinding medium code	A
Iron, sulphur and chlorine constituents	< 0.1 %

recommended approach angle	90 degrees
optimised for material	Steel
Propulsive equipment	Angle grinders
maximum circumferential speed	80 m/s
Type of product	Cutting disc

User data

	Suitability	V _c	ISO code
Alu Mg	suitable only under restricted conditions		
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable		
GG(G)	suitable only under restricted conditions		
CuZn	suitable only under restricted conditions		
Plastic, GRP	suitable only under restricted conditions		
Uni	suitable only under restricted conditions		
dry	suitable		