



Cutting disc, high-performance version PREMIUM*** EXTRA THIN, Disc Ø: 125mm



Order data

| | |
|--------------|---------------|
| Order number | 563165 125 |
| GTIN | 9009012018820 |
| Item class | 53T |

Description

Version:

The thinness of the disc allows **very quick cutting with low force** and optimum time saving.

Clean cut edges, virtually no burrs.

Very long life **high performance cutting disc** of the latest generation, comfortable handling due to rough free-grinding side faces.

Specification:

A60R-BFP.

Technical description

| | |
|-------------------|----------|
| Specification | A60R-BFP |
| Disc Ø | 125 mm |
| Bore Ø | 22.23 mm |
| Disc thickness | 1 mm |
| Shape description | flat |

| | |
|---|----------------|
| for material thicknesses | 3 - 5 mm |
| Grinding medium code | A |
| Iron, sulphur and chlorine constituents | < 0.1 % |
| recommended approach angle | 90 degrees |
| optimised for material | Steel |
| Propulsive equipment | Angle grinders |
| maximum circumferential speed | 80 m/s |
| Type of product | Cutting disc |

User data

| | Suitability | V _c | ISO code |
|--------------------------------|---|----------------|----------|
| Alu Mg | suitable only under restricted conditions | | |
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable | | |
| INOX | suitable | | |
| Ti | suitable | | |
| GG(G) | suitable only under restricted conditions | | |
| CuZn | suitable only under restricted conditions | | |
| Plastic, GRP | suitable only under restricted conditions | | |
| Uni | suitable only under restricted conditions | | |
| dry | suitable | | |

